

AQUA LUNG® GRÖSSENTABELLE TARIERJACKETS MEN | BC SIZE CHART MEN

Modell Model	Größe Size	Körpergröße Height	Gewicht Weight	Hüftumfang Waist range	"über-die-Schulter" Over the shoulder	Auftrieb in Litern Lift in Ltrs.
Axiom i3	XS	152 – 165	45 – 56	56 – 91	81 – 97	13
	S	157 – 170	54 – 70	68 – 104	86 – 102	13
	M	165 – 178	68 – 74	76 – 112	99 – 114	16
	ML	170 – 183	72 – 86	81 – 117	104 – 119	17
	L	170 – 188	82 – 95	89 – 124	109 – 124	19
	XL	188 – 196	89 – 108	94 – 129	114 – 130	21
	XXL	190 – 198	91 – 112	102 – 128	114 – 130	23
Axiom	XS	152 – 165	45 – 56	56 – 91	81 – 97	13
	S	157 – 170	54 – 70	68 – 104	86 – 102	13
	M	165 – 178	68 – 74	76 – 112	99 – 114	16
	ML	170 – 183	72 – 86	81 – 117	104 – 119	17
	L	170 – 188	81 – 95	89 – 124	109 – 124	19
	XL	188 – 196	89 – 108	94 – 129	114 – 130	21
	XXL	190 – 198	91 – 112	102 – 128	114 – 130	23
PRO LT	S	152 – 167	45 – 56	63 – 94	81 – 97	10
	S	158 – 173	54 – 70	27 – 42	86 – 102	12
	M	173 – 177	68 – 74	30 – 45	99 – 114	13
	ML	177 – 182	72 – 86	32 – 47	104 – 119	15
	L	182 – 189	81 – 95	35 – 50	109 – 124	20
	XL	189 – 198	88 – 108	37 – 52	114 – 130	25
DIMENSION i3	S	157 – 170	54 – 70	71 – 107	94 – 109	13
	M	170 – 178	68 – 75	81 – 117	102 – 117	22
	ML	178 – 183	73 – 86	84 – 119	107 – 122	22
	L	183 – 188	84 – 95	89 – 124	112 – 127	22
	XL	188 – 196	89 – 109	94 – 130	117 – 132	22
BALANCE	S	157 – 170	54 – 70	71 – 107	94 – 109	13
	M	170 – 178	68 – 75	81 – 117	102 – 117	18
	ML	178 – 183	73 – 86	84 – 119	107 – 122	18
	L	183 – 188	84 – 95	89 – 124	112 – 127	18
	XL	188 – 196	89 – 109	94 – 130	117 – 132	22
ZUMA	XXS/XS	142 – 165	41 – 57	71 – 109		10
	S/M	158 – 178	54 – 75	76 – 114		10
	ML/L	178 – 188	73 – 95	89 – 127		15
	XL/XXL	188 – 196	88 – 123	104 – 142		15
WAVE	XXS	25 – 34	63 – 86	64 – 81	25 – 32	8
	XS	152 – 165	45 – 56	71 – 94	79 – 97	11
	S	160 – 170	54 – 70	76 – 99	84 – 102	13
	M	165 – 178	68 – 79	86 – 109	91 – 109	15
	L	175 – 191	83 – 90	99 – 122	99 – 117	17
	XL	188 – 196	88 – 108	106 – 129	99 – 117	20


AQUA LUNG GRÖSSENTABELLE TARIERJACKETS LADIES | BC SIZE CHART LADIES

Modell Model	Größe Size	Körpergröße Height	Gewicht Weight	Hüftumfang Waist range	„über-die-Schulter“ Over the shoulder	Auftrieb in Litern Lift in Ltrs.
SOUL i3	XXS	152 – 165	41 – 57	66 – 96	81 – 96	10
	XS/SM	137 – 170	54 – 66	76 – 107	84 – 99	12
	MD	165 – 178	61 – 73	83 – 114	89 – 104	15
	ML	170 – 183	70 – 83	97 – 127	89 – 104	20
PEARL	XS	152 – 165	41 – 57	66 – 91	79 – 91	10
	S	157 – 170	54 – 66	76 – 96	84 – 97	13
	M	165 – 178	61 – 73	84 – 104	89 – 102	14
	ML	170 – 183	70 – 83	91 – 112	94 – 107	17
	L	170 – 183	79 – 95	107 – 127	97 – 109	20
LOTUS i3	S	157 – 170	54 – 66	76 – 96	84 – 97	13
	M	165 – 178	61 – 73	84 – 106	89 – 102	18
	ML	170 – 183	70 – 82	94 – 112	94 – 107	18
LIBRA	S	157 – 170	50 – 66	71 – 107	86 – 102	13
	M	165 – 178	64 – 75	81 – 117	91 – 107	18
	ML	178 – 183	73 – 86	84 – 119	91 – 107	18
ZUMA	XXS/XS	142 – 165	41 – 57	71 – 109		10
	S/M	158 – 178	54 – 75	76 – 114		10
	ML/L	178 – 188	73 – 95	89 – 127		15
	XL/XXL	188 – 196	88 – 123	104 – 142		15
WAVE	XXS	25 – 34	63 – 86	64 – 81	25 – 32	8
	XS	152 – 165	45 – 56	71 – 94	79 – 97	11
	S	160 – 170	54 – 70	76 – 99	84 – 102	13
	M	165 – 178	68 – 79	86 – 109	91 – 109	15
	L	175 – 191	83 – 90	99 – 122	99 – 117	17
	XL	188 – 196	88 – 108	106 – 129	99 – 117	20

Anleitung zum Maßnehmen | Measurement Instructions

Für die Abmessung des Taillenumfangs bei Männern wird normalerweise das Maßband um die Taille mittig auf Höhe des Beckenknochens gelegt. Das gilt nicht zur Abmessung bei Jackets. Für die Abmessung der Taille bei Jackets wird das Maßband auf Höhe des Bauchnabels, gerade über dem Beckenknochen um den Körper gelegt (Abbildung 1). Bei Frauen wird die Taille auch gerade oberhalb des Beckenknochens gemessen (Abbildung 1).

Zur Messung der Angabe „über die Schulter“ wird das Maßband entweder über die rechte oder linke Schulter gelegt und der Abstand von der Taillenlinie vorne zur Taillenlinie am Rücken gemessen (Abbildung 2). Auch hier gilt, dass die Taillenlinie gerade oberhalb der Beckenknochen liegt. Wenn Sie mit den Maßangaben in der Tabelle die spezifische Größe für den Taucher bestimmen, beachten Sie auch welche Art Tauchanzug der Taucher tragen wird. Rechnen Sie für Kaltwasseranzüge ca. 5 cm zur Angabe des Taillenumfangs hinzu.

Waist size in men is normally measured by placing the measuring tape around the waist, cresting the pelvic bone. This measurement is not accurate for BC fitting. The waist size in men should be measured at the height of the belly button just above the pelvic bone (Figure 1). Women's waist size is always measured just above the pelvic bone (Figure 1). This same measurement applies for BC fitting.

Over The Shoulder (OTS) measurement is taken by placing the measuring tape across either the right or left shoulder and reading the distance between the top of the waist line on the back to the top of the waist line in the front (Figure 2). Again, for this measurement in men the waistline is taken to be at the height of the belly button. When fitting the customer in his/her respective waist size and OTS range, inquire what thickness of wetsuit the BC is most likely to be worn with. Calculate about a 2" allowance for the waist measurements for thick, cold water suits.

ABBILDUNG 1: Messpunkte an der Taille.
FIGURE 1: Measuring points for waist size.



ABBILDUNG 2: Über die Schulter messen (OTS).
FIGURE 2: Measuring points for OTS length.

